



Hospital-Grade Tamper-Resistant Compact Design Receptacles, Back and Side Wire, 15A, 125V

Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

Voltage	125.0 V
---------	---------
