



## Pass and Seymour Tamper-Resistant Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle, Blue Part No. TR8300BLSP



Tamper-Resistant Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 20amp 125volt, Blue. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Internal screw-pressure-plate back and side wire capability.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

UPC Number	785007019421	Country Of Origin	China
Product Line	Pass & Seymour	Application Sector	Residential/Commercial

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Voltage	125 V	Connection	Side & Back Wire
Class	IG	Frequency Rating	60 Hz Hz
Phase	Single	Environmental Conditions	UL94 V2
Type of Indicators	LED, Audible Alarm		