



Pass and Seymour

20A 125V Hospital-Grade Tamper-Resistant Compact Duplex Receptacle, Back and Side Wire, Light Almond

Part No. TR8300HLA



Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V

## Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

## Technical Information

---

Is Tamper-Resistant              Yes                                      Amperage                      20 A

---

Number of Poles                      Double Pole                              Indoor/Outdoor              Indoor

---

Voltage                                      125.0 V

---