



**Pass and Seymour**  
**Tamper-Resistant Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Ivory**  
 Part No. TR8300ISP



Tamper-Resistant Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20amp 125volt, Blue. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Internal screw-pressure-plate back and side wire capability.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- Auto-ground clip assures positive ground.
- Backed-out tri-drive brass terminal screws for faster installation.
- Two back wire holes for additional wiring flexibility.
- .032 inch thick brass triple-wipe power contacts.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Phase	Single	Frequency Rating	60 Hz
Connection	Side & Back Wire	Class	IG

---

Amperage	20 A	Type of Indicators	LED, Audible Alarm
----------	------	--------------------	--------------------

---

Voltage	125.0 V	Environmental Conditions	UL94 V2
---------	---------	--------------------------	---------

---