



Pass and Seymour  
Hospital Grade Single Receptacles Tamper Resistant, Back and Side Wire, 20A, 125V, Black  
Part No. TR8301BK

Hospital Grade Single Receptacles Tamper-Resistant, Back and Side-Wire, 20A, 125A



## Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Dual mechanical shutter system to help prevent insertion of foreign objects.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Auto-ground eliminates the necessity to terminate grounding conductor to device

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, zinc-plated steel strap for added strength.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
--------------	----------------	-------	-------

Country Of Origin	Mexico
-------------------	--------

### Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
------------------	---------	------------------	----------

Product Height US	1.68 in
-------------------	---------

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Amperage	20 A
----------	------

---