



Pass and Seymour
Hospital Grade Single Receptacles Tamper Resistant, Back and Side Wire, 20A, 125V, White
Part No. TR8301W



Hospital Grade Single Receptacles Tamper-Resistant, Back and Side-Wire, 20A, 125A

Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Dual mechanical shutter system to help prevent insertion of foreign objects.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Auto-ground eliminates the necessity to terminate grounding conductor to device

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, zinc-plated steel strap for added strength.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007030990	Country Of Origin	Mexico
Standard	FEDSPEC		

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	1.68 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	20 A
----------	------
