



Tamper-Resistant Isolated Ground Hospital Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, Orange. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
  - Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
  - Internal screw-pressure-plate back and side wire capability.
  - Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
  - Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
  - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).
- Auto-ground clip assures positive ground.
  - Backed-out tri-drive brass terminal screws for faster installation.
  - Two back wire holes for additional wiring flexibility.
  - .032 inch thick brass triple-wipe power contacts.
  - For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007011616
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		

### Listing Agencies / 3rd Party Agencies

cULus Listing Number	140596	cULus Listed	Yes
----------------------	--------	--------------	-----

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

---

Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2

---