



Pass and Seymour  
TradeMaster® Tru-Universal Single Pole/3-Way Toggle Slide Dimmer, Preset, Light Almond  
Part No. TSD703PTULA



TradeMaster® Toggle Slide Tru-Universal Dimmer is designed for use with virtually any lamp type. This single pole 3-way switch is compatible with incandescent, halogen, ELV, CFL, or LED lighting options and can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability.

Features & Benefits

|   |  |
|---|--|
| Matches appearance of standard Pass and Seymour toggle switch       | All models are Single Pole/3-Way capable |
| Interchangeable face covers are available in seven different colors | Highest wattage rating                   |
| Lifetime warranty   |  |

Specifications

|                    |                                      |                    |  |
|--------------------|--------------------------------------|--------------------|--|
| General Info       |                                      |                    |  |
| Product Line       | Pass & Seymour                       | Color              | Light Almond   |
| Finish             | Gloss                                | UPC Number         | 785007216622   |
| Country Of Origin  | China                                | Features           | Auto-Calibration (Trim), Color Change Kit, High-End Trim (Dim Range), Low-End Trim (Dim Range) |
| Switch Type        | Single Pole 3-Way, Slider, Toggle    | Number of Switches | 1  |
| Application Sector | Commercial, Hospitality, Residential | Warranty Type      | Limited Lifetime Warranty  |

Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.73 in | Product Depth US | 1.4 in |
| Product Height US | 4.19 in |                  |        |

Technical Information

|                       |                                     |                       |   |
|-----------------------|-------------------------------------|-----------------------|---|
| Preset                | Yes                                 | Load Rating           | 120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent) |
| Dimming Compatibility | Forward or Reverse Selectable Phase | Frequency Rating      | 60 Hz   |
| Number of Gangs       | 1                                   | Bulb Compatibility    | CFL, Fluorescent, Halogen, Incandescent, LED  |
| Number of Poles       | Single Pole 3-Way                   | Wire Size             | #14 - #10 AWG   |
| Trim/Adjustment Level | Button with Slider                  | Requires Neutral Wire | Yes   |
| Indoor/Outdoor        | Indoor                              | Mounting Type         | Wall Box  |
| Wire Connection Type  | Screw Terminals                     | Voltage               | 120 VAC   |