



Pass and Seymour
TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Black
Part No. TSDCL303PBKCCV6



Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch	All models are Single Pole/3-Way capable
Interchangeable face covers are available in seven different colors	Highest wattage rating
Lifetime warranty	

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007432114
Country Of Origin	China	Features	Preset
Switch Type	Rocker, Slider	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

Technical Information

Amperage	2.5 A	Bulb Compatibility	CFL, Incandescent, LED
Number of Poles	3-Way, Single Pole	Wire Size	#14 - #10 AWG

Wattage

700 W
