



Pass and Seymour
TradeMaster® Toggle Slide Dimmer Low Voltage Single Pole/3-Way, 700VA, Gray
Part No. TSDLV703PGRY



700 VA, Preset, Single Pole/3-Way Toggle Slide Dimmer

Features & Benefits

Matches appearance of standard Pass & Seymour toggle switch

Interchangeable face covers are available in seven different colors

Lifetime warranty

All models are Single Pole/3-Way capable

Highest wattage rating

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Gloss	UPC Number	785007216158
Country Of Origin	China	Features	Color Change Kit, Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

Technical Information

Preset	Yes	Load Rating	120V 700VA (MLV - Halogen), 120V 700VA (MLV - Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	Halogen, Incandescent
Number of Poles	Single Pole 3-Way	Trim/Adjustment Level	Wheel
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC		