



Pass and Seymour  
TradeMaster® SSL7A-Compliant LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Light Almond  
Part No. TSDSSL7APLA



Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind, making it easier to adjust in the dark or on the run.

Compatible with CFL/LED and Incandescent/Halogen dimmable bulbs (with the exception of 0-10V LED drivers), these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

## Features & Benefits

No neutral wire required

Calibration button allows users to adjust minimum and maximum trim levels for a wide range of CFL and LED bulbs

New aesthetically pleasing ergonomic design allows for easier operation

Constant memory returns lights to previous levels after a power failure

Convenient operation – combines ON/OFF toggle switch with separate slider for dimming control

Screw-pressure-plate backwire terminals save time, space and money

Preset, Single Pole and 3-Way operation.

Lifetime warranty

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Gloss	UPC Number	785007216738
Country Of Origin	China	Features	Color Change Kit, High-End Trim (Dim Range), Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Preset	Yes	Load Rating	120V 2.1A 250W (CFL), 120V 2.1A 250W (LED), 120V 300W (Halogen), 120V 300W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Halogen, Incandescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG

Trim/Adjustment Level	Button	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC