



Wiremold  
Plug-In Outlet Center Unit / 120V/15A/6 O/L /15' cord  
Part No. UL206BD



Six outlets, rugged gray aluminum housing, 15A. 15' (4.6m) 14/3 SJT black cord with NEMA5-15 plug. Length 12 1/4" (311mm). Receptacle center-to-center 1 1/4" (32mm). Snap-on, slide-off mounting.

## Features & Benefits

Six outlets, rugged gray aluminum housing, 15A. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 12 1/4" (311mm). Receptacle center-to-center 1 1/4" (32mm). Snap-on, slide-off mounting.

## Specifications

### General Info

|                       |                                                       |                    |              |
|-----------------------|-------------------------------------------------------|--------------------|--------------|
| Product Line          | Wiremold                                              | UPC Number         | 786776510058 |
| Country Of Origin     | Mexico                                                | Receptacle Type    | Simplex      |
| Number of Receptacles | 6                                                     | Application Sector | Commercial   |
| Standard              | cULus Recognized: File E66421 Guide<br>XBYS XUHT VZCA | Type               | PIOC         |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 2.0 in  | Product Depth US | 1.89 in |
| Product Length US | 12.0 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

|                          |                        |                  |          |
|--------------------------|------------------------|------------------|----------|
| Phase                    | Single                 | Frequency Rating | 60 Hz    |
| Amperage                 | 15 A                   | Enclosure Type   | Aluminum |
| Mounting Type            | Snap-on, Slide-off     | Voltage          | 125 V    |
| Environmental Conditions | Dry interior locations |                  |          |