



Wiremold  
Plug-In Outlet Center Unit / Medical/Dental Grade/NOT for Patient Care areas/120V/15A/4 O/L /15' cord  
Part No. ULBH4-15



Four outlets. Rugged white aluminum housing. 15' (4.6m) 14/3 SJT white cord with NEMA5-15 plug. Length 10 3/4" (237mm). Receptacle center-to-center 1 1/2" (38mm). Snap-on, slide-off mounting. Not for use in critical care environments. NOTE: Not for use where Article 517 of NEC requires Hospital Grade Outlets.

## Features & Benefits

Four outlets. Rugged white aluminum housing. 6' (1.8m) 14/3 SJT white cord with NEMA5-15 plug. Length 10 3/4" (237mm). Receptacle center-to-center 1 1/2" (38mm). Snap-on, slide-off mounting. Not for use in critical care environments. NOTE: Not for use where Article 517 of NEC requires Hospital Grade Outlets.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776043402
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	4	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

### Dimensions

Product Width US	2.0 in	Product Weight US	3.0 lb
Product Length US	10.813 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

### Trade Programs

USMCA	Yes
-------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Phase	Single	Amperage	15 A
Enclosure Type	Aluminum	Mounting Type	Snap-on, Slide-off
Environmental Conditions	Dry interior locations		