




Wiremold
4047 Two-Gang Cover Single Round Opening
Part No. V4047JX



Accepts straight blade and single locking receptacles with face diameters of 1.56" - 1.58" (39mm - 40mm). NOTE: Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "CV" or the "G" color prefix to "CG" to denote the Canadian versions.

Features & Benefits

Accepts straight blade and single locking receptacles with face diameters of 1.56" - 1.58" (39mm - 40mm). NOTE: Certified to Canadian Safety Standards for sale in Canada

When ordering these products, change the "V" color prefix to "CV" or the "G" color prefix to "CG" to denote the Canadian versions

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776050868	Country Of Origin	United States
Application Sector	Commercial, Residential	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Blank Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.
Type	Raceway		

Dimensions

Product Width US	4.75 in	Product Weight US	0.38 lb
Product Length US	5.125 in		

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Voltage	600.0 V
---------	---------
