



On-Q
1x8 Enhanced Passive Video Splitter-Combiner
Part No. VM1002

High-performance splitter designed for digital cable, On Demand, Pay-per-View and high-speed cable Internet.



Features & Benefits

Strong 15 dB RF video amplification improves signal throughout the home system

DC passing between all ports.

Handles up to eight outputs and one input.

Bracket included.

Uses standard F type connectors.

1 GHz Bandwidth.

Specifications

General Info

Product Line	On-Q	UPC Number	804428021629
Country Of Origin	China		

Dimensions

Product Width US	3.6 in	Product Depth US	1.85 in
Product Length US	6.42 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Temperature Rating	-40° - 140° F	Insertion Loss	11.1 dB
--------------------	---------------	----------------	---------