



Long RangeSensor, Passe Infra, 24volt DC

Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

2 coverage patterns to choose from.

Wall mount or ceiling mount.

Adjustable sensitivity settings.

Digital time delay from 15 seconds to 30 minutes.

Dual-element, temperature-compensated pyroelectric sensor.

LED occupancy detection indicator.

Compatible with 120VAC or 277VAC, 60 Hz lighting systems.

Class 2 low-voltage device.

Positive detection indicator.

cULus listed.

5-year warranty.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007703801
--------------	----------------	------------	--------------

Country Of Origin	China	Application Sector	Commercial
-------------------	-------	--------------------	------------

Standard	UL Listed
----------	-----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Target Size	1050sq ft	Operating Cycles	100000
Body	Thermoplastic	Sensitivity	50/60 Hz
Load	120/230/277vac		
