



Wiremold
Wiremold 20GB306TR Tamper Resistant Plugmold Multioutlet System in White
Part No. WH20GB306TR



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

This product meets the material restrictions of RoHS.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

cULus Listed.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776174861	Country Of Origin	United States
Number of Receptacles	6	Application Sector	Residential/Commercial
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7	Type	Plugmold

Dimensions

Product Width US	36.0 in	Product Weight US	1.79 lb
Product Volume US	37.26 cu in	Product Depth US	0.75 in
Product Height US	1.38 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Frequency Rating	60 Hz	Amperage	15 A
Enclosure Type	Steel	Voltage	125 V
Environmental Conditions	Dry interior locations		