



Plate Kit For 2 Gang While-In-Use Weatherproof Cover

## Features & Benefits

Comply with NEC 2005 Section 406.8(B)(1) for wet locations covers, and conforms to NEMA 3R.

Covers mount vertically or horizontally.

Gasket made of closed cell foam, neoprene blend regular density, UL Rated HBF.

Single receptacle plate available in 1.405 inch and 1.595 inch openings.

Shallow covers accommodate up to 14/3 AWG extension cords.

Covers are self-closing as required by UL514C42.3.

Body, cover, and plates made of polycarbonate.

Mounting screws made of 302 stainless steel.

Deep model available for 20A locking plugs.

New trigger latch opens easily with one finger.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007139297
Country Of Origin	United States	Wall Plate Type	Custom
Application Sector	Industrial	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Wall Plate Accessories

### Listing Agencies / 3rd Party Agencies

cULus Listing Number	143222	cULus Listed	Yes
----------------------	--------	--------------	-----

### Technical Information

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Number of Outlets	2		