



This high quality insert is for use in all Keystone Wall Plates

Features & Benefits

Supports AnyPort Application Inserts, with most insert combinations compatible

Snap-in identification icons available

Recessed hex nut does not allow jack rotation

Recessed hex nut does not allow jack rotation

Previously P&S Part # KSFFBK

Outlets mount in On-Q Installation Brackets or low voltage mud rings

Fits decorator-style faceplates

Extra long for easy connections

Extra long for easy connections

Specifications

General Info

Color	White	UPC Number	804428025962
Country Of Origin	Taiwan, Province Of China	Product Line	On-Q
Package Quantity	50	Application Sector	Residential
Standard	UL ANSI/UL 1863		

Technical Information

Voltage	500 V	Connection	Molded high-impact flame retardant plastic Keystone insert
Conductor Range	0.022 to 0.042 (diameter) AWG	Cable Type	Coaxial

Temperature Rating -67 F to 311 F

Environmental Conditions 10 to 90 (relative humidity,
non-condensing)
