



Pass and Seymour
Weatherproof Cover for Flanged Inlet-Outlet
Part No. WPG1



Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet,
1.96-inch Diameter Opening to Accommodate 15/20A Straight Blade,
15A Turnlok®, 20403 Power Interrupter

Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.	Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.	WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
Covers fit all competitive inlets and outlets.	Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007065305
Country Of Origin	Mexico	Cover Type	Weatherproof
Features	Weatherproof	Application Sector	Industrial
Standard	UL listed	Type	Weatherproof Cover

Dimensions

Product Width US	2.85 in	Product Height US	4.57 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Outdoor
Mounting Type	Box Mounted	Box Cover Position	Vertical
Number of Outlets	1		
