



Pass and Seymour Thermoplastic Weatherproof Covers for Flanged Inlet-Outlet Part No. WPG2



Industrial Grade Weatherproof Lift Cover, 2.32-inch Diameter Opening to Accommodate 20A/30A Turnlok®, For Flanged Inlet/Outlet

Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.

Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.

Covers fit all competitive inlets and outlets.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.

Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007065329
Country Of Origin	Mexico	Cover Type	Weatherproof
Features	Weatherproof	Application Sector	Industrial
Standard	UL Listed, CSA	Type	Weatherproof Cover

Dimensions

Product Width US	2.85 in	Product Height US	4.57 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Outdoor
Mounting Type	Box Mounted	Box Cover Position	Vertical
Number of Outlets	1		