



Weather-Resistant Commercial Grade Receptacles, 20 amp, 125 volts, Ivory, WR20TRI

## Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

UV-resistant nylon face for longer life under adverse environmental conditions.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

WR marking on face as required by UL Standard.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Color	Gray	UPC Number	785007243222
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL 498

### Listing Agencies / 3rd Party Agencies

---

cULus Listed

Yes

cULus ListingNumber

140596

---

### Technical Information

---

Number of Poles

Double Pole

Voltage

125 V

---

Phase

3

Wire Size

10-14Awg

---

Number of Wires

3

---