



Weather-Resistant Tamper-Resistant Heavy Duty Spec Grade Single Receptacle, Back and Side Wire, 15A, 250V

Features & Benefits

| | |
|--|---|
| Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly | One-piece brass, triple-wipe power contacts for lasting retention |
| Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring | Impact-resistant nylon face and thermoplastic back body |
| Internal screw-pressure-plate back wire capable of accepting 14 to 10 AWG solid or stranded copper or copper-clad wire | Terminal compartments isolated from each other for positive conductor containment |
| Tri-drive terminal and mounting screws | Auto-ground clip assures positive ground |
| WR marking on face as required by UL Standard | |

Specifications

General Info

| | | | |
|-----------------|---|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Glossy | Country Of Origin | Mexico |
| Receptacle Type | Single | Number of Receptacles | 1 |
| Outlet Type | Weather-Resistant | Application Sector | Commercial |
| Standard | UL, CSA | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet, Tamper-Resistant, Weather-Resistant | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|---------------------|--------------|
| CSA Listed | Yes | cULus ListingNumber | E140596 |
| cULus Listed | Yes | CSA File Number | C22.2 No. 42 |

Technical Information

| | | | |
|----------------------|-------|--------------------------|-----------------------|
| Is Tamper-Resistant | Yes | Connection | Back and/or Side Wire |
| Amperage | 15 A | Wire Size | 14 - 10 AWG |
| Is Weather Resistant | Yes | Indoor/Outdoor | Outdoor |
| Mounting Type | Box | Voltage | 250.0 V |
| Connection Type | Wired | Environmental Conditions | Flammability: UL94 V2 |