



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 250V



Features & Benefits

Auto-ground clip assures positive ground.	WR marking on face as required by UL Standard.
Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.	Strap tabs wrap around face to prevent strap from separating from face and back body.
Tri-drive brass terminal screws.	Internal screw-pressure-plate back and side wire capability.
Two back wire holes for more wiring flexibility.	Heavy-duty, brass strap for added strength and ground conductivity.
UV-resistant nylon face for longer life under adverse environmental conditions.	Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.	.032 inch thick brass triple-wipe power contacts for lasting retention.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007243192
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498, FEDSPEC		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		