



Pass and Seymour
Wide Slide 0-10V Preset Dimmer with Integrated Power Pack, Tri-Color
Part No. WS4FBL3PTC



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts.

Low voltage pig tails labeled separately.

Green LED glows when OFF to make dimmer easy to find in the dark.

Wider slide control for easier dimming operation.

For covering patents, see www.legrand.us/patents.

Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control.

Preset, Single Pole and 3-Way Operation.

Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Built-in power pack included.

Specifications

General Info

Color	White, Light Almond, Ivory	UPC Number	785007047721
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	cULus, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Wattage	450 W	Number of Poles	Single Pole
---------	-------	-----------------	-------------

Voltage	120 V	Connection	Wire Leads
Frequency Rating	120VAC 60Hz Hz	Load	CFL/LED
Environmental Conditions	Humidity: Less than 95% non condensing		
