



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

## Features & Benefits

For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts	Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control
Low voltage pig tails labeled separately	Preset, Single Pole and 3-Way Operation
Green LED glows when OFF to make dimmer easy to find in the dark	Sleek, ergonomic Pass and Seymour Decorator style matches other Decorator devices
Wider slide control for easier dimming operation	Built-in power pack included

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007047738
Country Of Origin	China	Product Series	Decorator
Features	Color Change Kit, Low-End Trim (Dim Range)	Switch Type	Rocker, Slider
Number of Switches	1	Application Sector	Commercial, Hospitality, Residential
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Preset	Yes	Load Rating	120V 10A (Fluorescent), 120V 10A (LED), 277V 5A (Fluorescent), 277V 5A (LED)
Dimming Compatibility	0-10 V	Frequency Rating	60 Hz

Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120/277 VAC	Load Type	Fluorescent, LED
Environmental Conditions	Humidity: Less than 95% non condensing		