



Pass and Seymour

Wide Slide 0-10V Preset Dimmer with Integrated Power Pack, White
Part No. WS4FBL3PW



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

- For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts.
- Low voltage pig tails labeled separately.
- Green LED glows when OFF to make dimmer easy to find in the dark.
- Wider slide control for easier dimming operation.
- For covering patents, see www.legrand.us/patents.
- Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control.
- Preset, Single Pole and 3-Way Operation.
- Sleek, ergonomic P&S Decorator style matches other Decorator devices.
- Built-in power pack included.

Specifications

General Info

Color	White	UPC Number	785007047738
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	cULus, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Wattage	450 W	Number of Poles	Single Pole
Voltage	120 V	Connection	Wire Leads
Frequency Rating	120VAC 60Hz Hz	Load	CFL/LED
Environmental Conditions	Humidity: Less than 95% non condensing		