



Pass and Seymour
Wide Slide Fan Speed Control De-hummer, Single Pole, White
Part No. WSDH16W



1.6 AMP Wide Slide Dehummer Fan Control

Features & Benefits

- 4 Speed fan control with easy : slide to off" operation
- De-hummer feature virtually eliminates fan motor : hum" for quiet fan speed control
- Constant memory returns lights to previous level after a power failure
- 1.6A Rating single pole operation
- Supports other colors with WSKIT** interchangeable face plates

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007053586	Country Of Origin	China
Application Sector	Residential	Standard	CSA Listed, cULus, UL Listed

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Connection	Back Wired	Contact Rating	120VAC
Amperage	1.6 A	Number of Poles	Single Pole
Speed Range	Variable	Voltage	120.0 V
Environmental Conditions	Indoor Only		
