



Pass and Seymour
Wide Slide Interchangeable Face Magnetic Low-Voltage Dimmer, Tri-Color
Part No. WSLV703PTC



Wide Slide TradeMaster Interchangeable FaceMagnetic Low-VoltagePreset Dimmer. Single Pole/3-Way, 120V 700VA, includes 3 Interchangeable faces - Ivory, White and Light Almond. Pass and Seymour Dimmers save energy and extend bulb life , energy consumption reductions of up to 30% are possible.

Features & Benefits

Convenient operation - combines ON/OFF Decorator-style switch with separate slider for dimming control.

Higher ratings.

Screw-pressure-plate back wire terminals save time, space and money.

Interchangeable faces available in four colors: ivory,brown,black,light almond: (sold separately).

Constant memory returns lights to previous level after a power failure.

Single Pole and 3-way operation.

White only option also available (W).

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Operating Cycles	10000	Number of Poles	Single Pole
Wattage	700 W	Voltage	120 V

Load

700watt
