



Pass and Seymour
Wide Slide Interchangeable Face Magnetic Low-Voltage Dimmer, White Face Only
Part No. WSLV703PW



120V 700VA, Single Pole/3-Way Wide Slide Interchangeable Face Magnetic Low-Voltage Dimmer. Preset feature enables turning on directly to selected dimming level. Simple to operate this item is white face only.

Features & Benefits

Convenient operation - combines ON/OFF Decorator-style switch with separate slider for dimming control.

Sleek, ergonomic P&S Decorator-style matches other Decorator devices.

Screw-pressure-plate back wire terminals save time, space and money.

Interchangeable faces available in four colors: ivory, brown, black, light almond: (sold separately).

Constant memory returns lights to previous level after a power failure.

Higher ratings, Single Pole and 3-way operation.

Package: available with three face colors - Ivory, White, Light Almond: (TC).

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	White	UPC Number	785007009842
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	RoHS, UL Listed, CSA Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Wattage	700 W	Voltage	120 V
Connection	Screw Terminals	Frequency Rating	120VAC 60Hz Hz

Load	Magnetic Low Voltage	Environmental Conditions	Humidity: Less than 95% non condensing
------	----------------------	--------------------------	---
