



radiant Collection
Smart Tru-Universal Dimmer, Wi-Fi
Part No. WWRL50NICCV2



Take comfort in the convenience of controlling your lights from any smart device, from anywhere. The Smart Tru-Universal Dimmer, Wi-Fi offers precise light level control, and the ability to set scenes and schedules, all from any smart device. Or, just ask Alexa or Google to turn the lights on for you. Combining classic design and advanced functionality with simple connection among existing smart home solutions using your home's wireless network, Smart Lighting from the radiant® Collection sets the exact lighting you want, when and where you need it. Tru-Universal Dimmers works with virtually any 120V dimmable bulb or fixture, adjusting to the exact light level you want, without the flicker.

Features & Benefits

Control lights from smart phones and tablets with the Smart Lights app. Even schedule lights to turn on/off automatically, create groups or set scenes.

Works with a home's existing secure Wi-Fi network (WPA2). Also includes out-of-the-box connectivity with other smart devices through OCF certification.

Installs easily in place of an existing switch or dimmer, neutral wire required. Operates any 120V dimmable light or fixture.

Just ask Amazon Alexa or Google Assistant to turn on the lights.

Know your home is secure, even when you're away.

Set the exact lighting level you need.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look.

Specifications

General Info

Color	Nickel	UPC Number	785007235920
Country Of Origin	China	Product Line	Pass & Seymour
Number of Switches	1	Warranty Type	Limited Lifetime Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Wattage	700 W	Number of Poles	Multi-Location, Single Pole, 3-Way
Number of Gangs	1	Voltage	120 V
Mounting Type	Box		
