



This Cisco XENPAK-10GB-SR compatible XENPAK transceiver provides 10GBase-SR throughput up to 300m over multi-mode fiber (MMF) at a wavelength of 850nm using a SC connector. Our transceiver is guaranteed to be 100% compatible with the equivalent Cisco transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Cisco, as well as to comply with multi-source agreement (MSA) standards to ensure seamless network integration.

**Please Note:** Installing Legrand transceivers does not void your network equipment warranty. Network equipment manufacturers all have guidelines stating that warranty support on their products will not be affected by installing a Legrand or any third party transceiver.

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120668053	Country Of Origin	United States
Application Sector	Commercial/Industrial	Standard	IEEE 802.3, FCC 47 CFR
Type	Transceiver		

Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----

Technical Information

Operating Temperature Min	-40 °C	Operating Temperature Max	85 °F
Data Transfer Rate	1.25 Gbps	Connector Type	RJ45
Form Factor	SFP-T		