



Ortronics

Cisco XFP-10G-MM-SR Compatible 10GBase-SR XFP Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)

Part No. XFP-10G-MM-SR-L

Cisco XFP-10G-MM-SR Compatible 10GBase-SR XFP Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line

Ortronics

Country Of Origin

China

Type

Transceiver

Technical Information

Fiber Optic Cable Type

Multimode

Operating Temperature Min

-40 C

Operating Temperature Max

85 C

Data Transfer Rate

10 Gbps

Connector Type

LC Duplex

Wavelength

850nm

Form Factor

XFP