PASS & SEYMOUR®

20A 125V Plug Load Dual Controlled Tamper-Resistant GFCI with Safelock Protection



Reinventing Safety All Around

2097TRCD

The Pass & Seymour® Dual-Controlled Self Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

Features & Benefits

Patented SafeLock® Protection: for if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects.

Side or internal screw-pressure-plate back wire termination with #14 – #10 AWG stranded or solid, copper or copper-clad conductors.

Two back-wire holes per termination add wiring flexibility, eliminate pigtailing and save box space.

Code compliant controlled receptacle marking with abrasion resistant ink is NEMA approved and compliant with 2023 NEC, CA Title 24, Part 6: Building Energy Efficiency Standards, ASHRAE 90.1 Energy Efficiency Standard 90.1, and the 2021 International Energy Conservation Code (IECC).

Captive screws make for easier installation.



2097TRCDLA

Ground terminal clamp allows for fast installation.

Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

The indicator light flashes if the device fails the self-test, signaling that the GFCI should be replaced.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Auto-ground clip assures a positive ground to metal box.

The most durable GFCI available. Exceeds UL943 voltage surge requirements.

3rd Party Compliance

cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, Standard UL943 for GFCIs. Federal Specification WC596, Hospital Grade. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 for GFCIs. Conforms to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Dielectric Voltage	Withstands 1500V minimum
Maximum Working Voltage	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC
Mechanical	
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of device
Environmental	
Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2
Material Specs	
Face:	Nylon
Body:	Nylon
Contacts:	.03" Brass (.8)
Mounting Straps:	Galvanized Steel
Terminal Screws:	Nickel-Plated Steel #8 - 32
Hex Head Grounding Screw:	Steel (Green)
Flat Head Mounting Screws:	Zinc-Plated Steel
Test/Reset Buttons:	Nylon
Auto-Ground Clip:	Brass Alloy
**Tamper-Resistant Shutter:	Thermoplastic



Dimensions for 20 Amp

Warranty: 1 year

Ordering Information

Dual Controlled Specification Grade Self-Test GFCI's

Catalog Number	Description	Rating	Color Number
2097TRCD*	Marked controlled spec grade tamper-resistant 20 Amp Duplex GFCI	20A, 125V	I, W, GRY, BK, RED, LA, BL, GN

NEMA 5-20R

*** Color Designation**

I - Ivory
W- White
GRY- Gray
BK- Black
RED- Red
LA- Light Almond
BL- Blue
GN- Green

For more information on these and other P&S products refer to our Catalog or visit our website.

Field Uses/Vertical Markets

- **Industrial**
- **Retail**
- **Healthcare**
- **Off ice**
- **Education**
- **Hospitality/Lodging**
- **Institutional**
- **Multiple Dwelling**

Also available

- **USB Charging Devices**
- **PlugTail® Devices**
- **Surge Protective & Isolated Ground Devices**
- **Ground Continuity Monitoring Devices (GCM)**
- **Straight Blade Plugs & Connectors**
- **Turnlok® Locking Devices**
- **Weatherproof Boxes & Covers**
- **IEC 309 Industrial Products**
- **Flexcor® Wire Mesh Grips**
- **Night Lights**

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1-877-295-3472
www.legrand.us

Canada
1-844-977-3783
www.legrand.ca

FOLLOW US

© Copyright 2025 Legrand All Rights Reserved