Clarity TracJack Copper Jack

Clarity TracJack (TJ) Cat6, T568A/B

Clarity 6 TracJack, ETL verified to TIA Category 6 component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity 6 patch cords for optimum performance.

Features and Benefits

- **Guaranteed Performance Levels:** ETL verified to TIA Category 6 component specification
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion
- **Enables High-Power PoE:** Up to 100W and 1.5 amps per circuit trace
- **Easy Lace IDC Design:** Reduces wiring time
- **Front Loading:** Preferred mounting for panels
- **Icon Compatible, Cat6 Marking on Jack Face:** Supports 606 designation requirements
- **Standard TracJack Footprint:** Fits in all TracJack faceplates and housings
- **Center Tuned Design:** Transparent interface with Clarity 6 patch cords

Clarity TracJack Copper Jack

BASE PN: TJ600-xx

ORDERING INFORMATION

Item Number	Description
TJ600	Clarity TracJack (TJ) Cat6, T568A/B, Fog White
TJ600-00	Clarity TracJack (TJ) Cat6, T568A/B, Black
TJ600-13	Clarity TracJack (TJ) Cat6, T568A/B, Ivory
TJ600-22	Clarity TracJack (TJ) Cat6, T568A/B, Light Red
TJ600-23	Clarity TracJack (TJ) Cat6, T568A/B, Light Orange
TJ600-24	Clarity TracJack (TJ) Cat6, T568A/B, Light Yellow
TJ600-25	Clarity TracJack (TJ) Cat6, T568A/B, Light Green
TJ600-26	Clarity TracJack (TJ) Cat6, T568A/B, Light Blue
TJ600-27	Clarity TracJack (TJ) Cat6, T568A/B, Purple
TJ600-36	Clarity TracJack (TJ) Cat6, T568A/B, Blue
TJ600-42	Clarity TracJack (TJ) Cat6, T568A/B, Red
TJ600-43	Clarity TracJack (TJ) Cat6, T568A/B, Orange
TJ600-44	Clarity TracJack (TJ) Cat6, T568A/B, Yellow
TJ600-45	Clarity TracJack (TJ) Cat6, T568A/B, Green
TJ600-68	Clarity TracJack (TJ) Cat6, T568A/B, Light Gray
TJ600-78	Clarity TracJack (TJ) Cat6, T568A/B, Dark Gray
TJ600-88	Clarity TracJack (TJ) Cat6, T568A/B, White
TJ600-99	Clarity TracJack (TJ) Cat6, T568A/B, Wiremold Ivory

GENERAL INFORMATION

Color	Fog White, Black, Ivory, Light Red, Light Orange, Light Yellow, Light Green, Light Blue, Purple, Blue, Red, Orange, Yellow, Green, Light Gray, Dark Gray, White, Wiremold Ivory
Country Of Origin	Mexico
Type	Unshielded RJ45
PEP	Yes - Product Environmental Profile
Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant

DIMENSIONS

Product Width	0.73 in / 16.00 mm
Product Height	0.92 in / 19.56 mm
Product Length	1.1 in / 40.89 mm

TECHNICAL INFORMATION

Construction	Plastic
Use Type	Modular TJ Panel and Housing
Compatibility	568 A/B
Impedance	100Ω
Gauge	22-26 AWG
Operating Temp	-10° + 60° C

© 2023 Legrand. All rights reserved. The industry-leading brands of Approved Networks, Ortronics, Raritan, Server Technology, and Starline empower Legrand's Data, Power & Control to produce innovative solutions for data centers, building networks, and facility infrastructures. Our division designs, manufactures, and markets world-class products for a more productive and sustainable future. The exceptional reliability of our technologies results from decades of proven performance and a dedication to research and development.