

PlugTail® Receptacle & Switch Connectors

Connect with the product line that keeps growing.

For accurate, faster jobs that require significantly less labor, choose from a wide variety of PlugTail connectors designed specifically to work with our PlugTail line of receptacles, switches and sensors.

With an array of lengths, color options and connector types that cover a multitude of onsite and prefab needs, experience the ease and efficiency of using PlugTail devices on your next project to help you finish in record time.



PlugTail® with XHHW-2 Wire

Available with orange connector head and is NEC 517.160 code compliant.



PTRA6STRX21



PTRA6STROR

Faster Installations

Pre-stripped connector leads fasten to conductors more easily than standard pigtails.

Finger-Safe Design

No exposed terminals provide protection before, during and after installation.

Secure Terminations

Large crimped and welded brass contacts provide a snug fit on device blade terminals.

Safe, Durable Housing

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL listed, finger-safe design.

Reliable Connection

Audible snapping latch confirms connection and allows easy release.

Space-Saving Fit

Right-angle connectors sit flush with the device back to maximize box space.

Permanent Identification

Exclusive patented circuit label on back enables lasting circuit identification.

Switch Compatibility

Connectors deliver a 3-wire solution for single pole and a 4-wire solution for 3-way applications.

Productivity Add-Ons

Boost efficiency for 4-port push-in connectors, fork terminal on ground wire, colored connector heads and longer-length pigtail solutions.

CATALOG #	DEVICE TYPE	WIRE TYPE	LENGTH OF LEAD	PACKAGING STYLE	SPECIAL FEATURE
PTRA6SOL	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTRA6SOLB12	Receptacle	#12 AWG Solid THHN	12 in.	25 ct. Box	12 IN Pre-stripped pigtail leads
PTRA6SOLB25	Receptacle	#12 AWG Solid THHN	25 in.	25 ct. Box	25 IN Pre-stripped pigtail leads
PTRA6SOLBP	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTRA6SOLG	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; Fork terminal pre-installed on ground wire
PTRA6SOLNA	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; NAFTA Compliant
PTRA6STR	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTRA6STRB12	Receptacle	#12 AWG Stranded THHN	12 in.	100 ct. Box	Pre-stripped pigtail leads
PTRA6STRB180	Receptacle	#12 AWG Stranded THHN	15 in.	25 ct. Box	15 FT Pre-stripped pigtail leads
PTRA6STRB25	Receptacle	#12 AWG Stranded THHN	25 in.	25 ct. Box	25 IN Pre- stripped pigtail leads
PTRA6STRBP	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTRA6STRG	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; Fork terminal pre-installed on ground wire
PTRA6STRNA	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; NAFTA Compliant
PTRA6STRNABL	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; blue connector base for UPS and Surge Protective applications
PTRA6STRNARED	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; red connector base for emergency circuit applications
PTS6SOL3	1P Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL3277	1P, 277-Volt Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL3BP	1P Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6SOL4	3W Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL4277	3W, 277-Volt Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL4BP	3W Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR3	1P Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR3277	1P, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR3277BP	1P, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR3BP	1P Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR4	3W Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR4277	3W, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR4277BP	3W, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR4BP	3W Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTRA6STRX21	Receptacle	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads; Complies with NEC 517.160 for isolated power areas. Ideal for Low leakage circuits. (Brown/Yellow), (Orange/ Blue), (Green/Yellow)
PTRA6STRX220R	Receptacle	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads; orange connector base for Isolated Ground applications, Ground (Green / Yellow)
PTRA6STRORB	Receptacle	# 12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires, orange connector base for Isolated Ground applications
PTRA6STROR	Receptacle	# 12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; orange connector base for Isolated Ground applications
PTRA6SOLOR	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads. orange connector base for Isolated Ground applications
PTRA6STRX2	Receptacle	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads.
PTS6STR3277X2	1P, 277-Volt Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads., 1P 277v Switch
PTS6STR3BPX2	1P, 277-Volt Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads. 1P Switch, 4-port push-in connectors on all 3 wires
PTS6STR3X2	1P Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads. 1P Switch
PTS6STR4277X2	3W, 277-Volt Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads. 3W 277v Switch
PTS6STR4BPX2	3W, 277-Volt Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads. 4-port push-in connectors on all 3 wires
PTS6STR4X2	3W Switch	# 12 AWG Stranded XHHW-2	6 in.	25 ct. Box	XHHW-2 Pre-stripped pigtail leads.
PTRA6SOLBP64	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-Stripped pigtail leads; Wago 6-port push-in (G) connector, 4-port push-in (H/N) connector

