**PASS & SEYMOUR®**

# 50A Turnlok® Plugs and Connectors

**CS6365C Plug & CS6364C Connector**

## Safe and Durable 50A Power Connections

Our 50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. 50A Turnlok Plugs and Connectors feature a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.

## Features & Benefits

### Feature:

- Quality Materials, durability, and time-tested design.
- Push, twist and lock design that eliminates the need for time-consuming threading
- Industrial-Strength Brass Alloy Plug Blades and Connector Contacts: Resist heat rise and provide excellent conductivity.
- Nylon 66 shell material is impact and UV-resistant
- Features an adjustable cord clamp strategically located outside the back body to accommodate various cord sizes
- Device's same-plane hex terminations make every termination faster and safer
- Integral flexible rubber cord grommet provides protection from oils, water or chips entering the wiring chamber

## Vertical Markets

- **Construction Sites**
- **Outdoor Events**
- **Entertainment Venues**
- **Disaster Relief**
- **Data Center**

## Compliance

**cULus Listed Wiring Assembly:** File E146159.
Standard UL498 Attachment Plugs and Receptacles

## Technical Information

| Performance | |
|---|---|
| **Electrical** | |
| Dielectric Withstand Voltage | Withstands 3000V |
| Number of Wires | 3/4 |
| Number of Poles | 2/3 |
| Frequency | 60 Hz |
| Voltage Range | 125-600V |

| | |
|---|---|
| **Mechanical** | |
| Terminal Identification | “GR” and Green color = Ground, “WH” and White color = Neutral, “X”, “Y”, “Z” = Hot |
| Terminal Accommodation | #8 AWG min. - #4 AWG max. |
| Product Identification | Amperage, Voltage, 3rd Party Compliance, hot stamped onto device |

| | |
|---|---|
| **Environmental** | |
| Operating Temperature | Maximum continuous +75°C, minimum -40°C without impact |
| Maximum Humidity | 95% |
| Flammability | UL94 V2 |

| Material Specs | |
|---|---|
| Face | Nylon 66 |
| Body | Nylon 66 |
| Contacts | .05” Brass |
| Mounting Strap | Galvanized Steel |
| Terminal Screws | Nickel-Plated Steel #5/16 – 24 |

### Warranty

1 Year

## Ordering Information

| | Ratings | | | |
|---|---|---|---|---|
| Catalog No./Item | A. | V. | Description/Color | Cord Diameter |
| **Connectors California Standard** | | | | |
| **CS6360C** | 50A | 125V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS6364C** | 50A | 125/250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8164C** | 50A | 3ø480V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8264C** | 50A | 250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8364C** | 50A | 3ø250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8464C** | 50A | 480V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **Plugs California Standard** | | | | |
| **CS6361C** | 50A | 125V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS6365C** | 50A | 125/250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8165C** | 50A | 3ø480V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8265C** | 50A | 250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8365C** | 50A | 3ø250V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CS8465C** | 50A | 480V | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **Connectors Corrosion Resistant** | | | | |
| **CR6360C** | 50A | 125V | Yellow Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CR6364C** | 50A | 125/250V | Yellow Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **Plugs Corrosion Resistant** | | | | |
| **CR6361C** | 50A | 125V | Yellow Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **CR6365C** | 50A | 125/250V | Yellow Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **Connectors 50A Turnlok** | | | | |
| **3762C** | 50A | 600VAC/250VAC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **3764C** | 50A | 600VAC/250VDC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **7764C** | 50A | 600VAC/250VDC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **Plugs 50A Turnlok** | | | | |
| **3763MC** | 50A | 600VAC/250VAC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **3765C** | 50A | 600VAC/250VDC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |
| **7765C** | 50A | 600VAC/250VDC | Black Back, White Front Body | .700"-1.200" 8AWG-4AWG |




**Disclaimer:** Not compatible with flip lid cover receptacles including 7770 & 7770GRY

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

**Legrand, North America**
60 Woodlawn Street
West Hartford, CT 06110
877-295-3472
www.legrand.us

**Canada**
844-977-3783
www.legrand.ca

FOLLOW US

CS3314 — May 2026 — For latest specs visit www.legrand.us/passandseymour

©2024 Legrand All Rights Reserved