adorne®
Tamper-Resistant Outlet

ARTR152, ARTR202

Tamper-Resistant Outlet

adorne® Tamper-Resistant Outlets include a tamper-resistant design featuring a patented shutter system, keeping children safe by preventing them from pushing small objects into the outlet. The shutters are molded a dark color so that they fade into the background while keeping users safe. Outlets and GFCIs are available in full and plus-size versions. All adorne 15A outlets have a 20A feed or pass-through allowing them to be installed on 20A circuits, such as in kitchens, bathrooms, etc.



FEATURES & BENEFITS

adorne devices fit in all existing NEMA-approved wallboxes.

Heavy gauge steel frame is grounded via factory installed 12AWG ground lead. Device and metal wall plates are self-grounded to frame.

Device snaps into the frame and self-aligns without any screws.



STANDARD WALLBOX

DEVICE

FRAME

adorne devices can be installed in any existing standard wallbox.

Wall plate snaps onto frame; no screws required.

Modular system solves device alignment problems, improving fit and finish in multi-gang installations.

Wall plate and frames available in 1-6 gang sizes.

Backwire terminal screws are recessed into back of body.

WALL PLATE

ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	RATING	NEMA	COMPLIANCE	COLORS	COO
ARTR152M4	2-Module Tamper-Resistant Outlet	15A, 125V	5-15R		Magnesium	China
ARTR152W4	2-Module Tamper-Resistant Outlet	15A, 125V	5-15R		White	China
ARTR152G4	2-Module Tamper-Resistant Outlet	15A, 125V	5-15R		Graphite	China
ARTR202M4	2-Module Tamper-Resistant Outlet	20A, 125V	5-20R		Magnesium	China
ARTR202W4	2-Module Tamper-Resistant Outlet	20A, 125V	5-20R		White	China
ARTR202G4	2-Module Tamper-Resistant Outlet	20A, 125V	5-20R		Graphite	China

VERTICAL MARKETS

- Residential
- Hospitality
- Luxury Office
- Light Commercial

COMPLEMENTARY PRODUCTS

adorne® also offers Paddle Style Dimmers and Fan Control Devices to pair with our Paddle Style Switches for an overall, aesthetically pleasing and multi-functional installation.

adorne® Wall Plates provide the perfect complement to adorne Switches, Dimmers, Outlets, and Accessories. The collection includes a variety of finishes, from metals to leather and wood, as well as plastic plates that are available in contemporary and classic colors.

Each wall plate is packaged with a metal frame to enable easy installation when paired with a device. All plates are screwless and simply snap onto the included metal frame.

All adorne wall plates are UL and ETL-approved.

2-Module Paddle Dimmer

2-Module Paddle Fan Speed Control

1-Module Paddle Switch

TECHNICAL SPECIFICATIONS



3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498,

Performance

ELECTRICAL

Dielectric Voltage	Withstands 1500V minimum
Maximum Working Voltage	125VAC
Current Rated	15A interrupting at full-rated current
Temperature Rise	30°C Maximum at full-rated current

MECHANICAL

Back Wire	With internal pressure plates, #8-32 screw
Terminal Accommodations	#14AWG-#12AWG

ENVIRONMENTAL

Flammability	UL94 V2



Materials

Face	Polycarbonate	Terminal	Brass
Back Body	Polycarbonate	Termination	Steel Plated Scews
Contacts	Silver		

Warranty

Limited Lifetime Warranty

COMPLEMENTARY DEVICES & ACCESSORIES

sofTap™
Switches & Dimmers – designed with an innovative micro-movement that turns lights on and off with just a soft "tap" of the finger.

SensaSwitch™
Switches & Dimmers – Sensor turns lights on when you enter a room and off when you leave. (Also available in Manual-ON/Auto-OFF format.)

Whisper™
Switches & Dimmers – A smart design that features elegant lines and a quiet, fluid motion.

Touch™
Switches & Dimmers – A stunning translucent face works just like an iPhone® — simply touch your finger on the circle to turn lights on and off.



Paddle™
Switches, Dimmers & Fan Speed Controls – A wide, graceful curve works with a simple up-and-down motion, allowing you to turn lights on and off with ease.



Wave™
Switches – Smart technology combined with sleek, modern design. Simply wave your hand to turn lights on and off.

Push™
Switches – A tactile, finger-sized impression lets you turn lights on and off with a simple push-button motion.



Tamper-Resistant Outlets/ Tamper-Resistant GFCI Outlets

USB Charging Outlets

Nightlight/Portable Nightlight Flashlight

PLUS: Compatible Wall Plates, Accent Lights, Locator Lights, Under-Cabinet Lighting System

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US

©2019 Legrand All Rights Reserved SF20261R1