legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3F61RS**

AISI Type 316L **T**









GENERAL INFORMATION

NEMA TRAY TYPE: Two Rail Ladder
NEMA CLASS: 20C
MATERIAL: AISI Type 316L Stainless Steel
SIDE RAIL: 6" high with 1 3/4" top flange
LOAD DEPTH: 5"
BOTTOM: 1" wide box rung
FINISH: Plain
CONSTRUCTION: Arc welded
TRAY SERIES: Series 2 (5" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 3.4185in^3 S x-x = 1.2324in^4

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	5.36
9	5.54
12	5.71
18	6.05
24	6.39
30	7.25
36	7.69

**Based on 9" rung spacing*

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
		564	0.31	400	0.54	278	0.77	204	1.05	156	1.38	123	1.74	100	2.15	81	2.54	63	2.83						

CATALOG NUMBERING EXAMPLE:

09 - 3F61 - 0020 - 36

Bottom Type
06 – 6" Rung Spacing
09 – 9" Rung Spacing*
12 – 12" Rung Spacing
18 – 18" Rung Spacing
** Standard rung spacing*

Tray System Number

Length
0010 – 10'-0"
0012 – 12'-0"
0020* – 20'-0"
0024 – 24'-0"
** Standard for Series 2*

Width
06 – 6"
09 – 9"
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil