adorne®
SofTap Style Dimmers

ADTP1103H, ADTP4FBL3P, ADTP703H

SofTap Style Dimmers

adorne® SofTap Style Dimmers feature an innovative micro-movement that turns lights on and off with just a soft "tap" of the finger. Dimmers include a unique paddle to adjust light levels.

SofTap products include a Locator Status Light which add illumination and make it easier to locate in the dark.

FEATURES & BENEFITS

adorne devices fit in all existing NEMA-approved wallboxes.

Heavy gauge steel frame is grounded via factory installed 12AWG ground lead. Device and metal wall plates are self-grounded to frame.

Device snaps into the frame and self-aligns without any screws.



STANDARD WALLBOX

FRAME

DEVICE

WALL PLATE

Wall plate snaps onto frame; no screws required.

Modular system solves device alignment problems, improving fit and finish in multi-gang installations.

adorne devices can be installed in any existing standard wallbox.

Wall plate and frames available in 1-6 gang sizes.

Backwire terminal screws are recessed into back of body.

ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	RATING	COMPATIBLE LOADS	COMPLIANCE	COLORS	COO
ADTP1103HM4	Single-Pole/ 3-Way 2-Wire	1100W	Incandescent, Halogen		Magnesium	China
ADTP1103HW4	Single-Pole/ 3-Way 2-Wire	1100W	Incandescent, Halogen		White	China
ADTP4FBL3PM2	Single-Pole/ 3-Way	0-10V	0-10V Light Fixtures		Magnesium	China
ADTP4FBL3PW2	Single-Pole/ 3-Way	0-10V	0-10V Light Fixtures		White	China
ADTP4FBL3PG4	Single-Pole/ 3-Way	0-10V	0-10V Light Fixtures		Graphite	China
ADTP703HM4	Single-Pole/ 3-Way 2-Wire	700W	Incandescent, Halogen		Magnesium	China
ADTP703HW4	Single-Pole/ 3-Way 2-Wire	700W	Incandescent, Halogen		White	China

COMPLEMENTARY PRODUCTS

adorne® also offers Paddle Style Dimmers and Fan Control Devices to pair with our Paddle Style Switches for an overall, aesthetically pleasing and multi-functional installation.

adorne® Wall Plates provide the perfect complement to adorne Switches, Dimmers, Outlets, and Accessories. The collection includes a variety of finishes, from metals to leather and wood, as well as plastic plates that are available in contemporary and classic colors.

Each wall plate is packaged with a metal frame to enable easy installation when paired with a device. All plates are screwless and simply snap onto the included metal frame.

All adorne wall plates are UL and ETL-approved.

2-Module
Paddle Dimmer

2-Module
Paddle Fan
Speed Control

1-Module
Paddle Switch

VERTICAL MARKETS

- Residential
- Hospitality
- Luxury Office
- Light Commercial

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, UL1472, File E95219



Performance

ELECTRICAL	
Supply Voltage	120 VAC
Ratings	700W-1100W Incandescent/Halogen/MLV
Frequency	60Hz
Installation	Single Pole or 3-Way
MECHANICAL	
Enclosure Material	Polycarbonate
ENVIRONMENTAL	
Application	Indoor Use Only



Materials

Paddle	Polycarbonate	Terminal	Brass
Back Body	Polycarbonate	Termination	Steel Plated Scews
Contacts	Silver		

Warranty

Lifetime Limited Warranty

COMPLEMENTARY DEVICES & ACCESSORIES

sofTap™
Switches & Dimmers – designed with an innovative micro-movement that turns lights on and off with just a soft "tap" of the finger.



Wave™
Switches – Smart technology combined with sleek, modern design. Simply wave your hand to turn lights on and off.

SensaSwitch™
Switches & Dimmers – Sensor turns lights on when you enter a room and off when you leave. (Also available in Manual-ON/Auto-OFF format.)

Push™
Switches – A tactile, finger-sized impression lets you turn lights on and off with a simple push-button motion.

Whisper™
Switches & Dimmers – A smart design that features elegant lines and a quiet, fluid motion.



Tamper-Resistant Outlets/ Tamper-Resistant GFCI Outlets

Touch™
Switches & Dimmers – A stunning translucent face works just like an iPhone® — simply touch your finger on the circle to turn lights on and off.

USB Charging Outlets



Paddle™
Switches, Dimmers & Fan Speed Controls – A wide, graceful curve works with a simple up-and-down motion, allowing you to turn lights on and off with ease.

Nightlight/Portable Nightlight Flashlight

PLUS: Compatible Wall Plates, Accent Lights, Locator Lights, Under-Cabinet Lighting System

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US

©2019 Legrand All Rights Reserved SF20248R1