legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3604RS**



RAIL CROSS SECTION



RUNG CROSS SECTION



CONNECTOR



AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE: Two Rail Ladder
NEMA CLASS: 12C
MATERIAL: AISI Type 304L Stainless Steel
SIDE RAIL: 6" high with 1" top flange
LOAD DEPTH: 5"
BOTTOM: 1 1/4" wide hat rung
FINISH: Plain
CONSTRUCTION: Resistance welded
TRAY SERIES: Series 1 (2" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 1.7873in^3 S x-x = 0.6733in^4

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	3.32
9	3.49
12	3.66
18	4.00
24	4.34
30	5.20
36	5.65

**Based on 9" rung spacing*

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
400	0.14	225	0.24	144	0.38	100	0.54																		

CATALOG NUMBERING EXAMPLE:

09-3604-0012-36

Bottom Type
06 – 6" Rung Spacing
09 – 9" Rung Spacing*
12 – 12" Rung Spacing
** Standard rung spacing*

Tray System Number

Length
0010 – 10'-0"
0012* – 12'-0"
** Standard for Series 1*

Width
06 – 6"
09 – 9"
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil

legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3604SF**



RAIL CROSS SECTION



CONNECTOR



AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE: Solid Flat
NEMA CLASS: 12C
MATERIAL: AISI Type 304L Stainless Steel
SIDE RAIL: 6" high with 1" top flange
LOAD DEPTH: 5"
BOTTOM: Solid Flat
FINISH: Plain
CONSTRUCTION: Arc welded
TRAY SERIES: Series 1 (2" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: ⅜ in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 1.7873in^3 S x-x = 0.6733in^4

TRAY WIDTH (IN.)	TRAY WEIGHT (LBS./FT.)
6	3.99
9	4.49
12	5.00
18	6.01
24	7.02
30	8.02
36	9.28

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
400	0.14	225	0.24	144	0.38	100	0.54																		

CATALOG NUMBERING EXAMPLE:

SF-3604-0012-36

Bottom Type
SF – Solid Flat

Tray System Number

Length
0010 – 10'-0"
0012* – 12'-0"
** Standard for Series 1*

Width
06 – 6"
09 – 9"
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil