legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3476RS**









AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE: Two Rail Ladder
NEMA CLASS: 20A, 16B
MATERIAL: AISI Type 304L Stainless Steel
SIDE RAIL: 4" high with 1 3/4" top flange
LOAD DEPTH: 3"
BOTTOM: 1 1/4" wide hat rung
FINISH: Plain
CONSTRUCTION: Resistance welded
TRAY SERIES: Series 2 (5" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 1.0593in^3 S x-x = 0.5860in^4

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	3.54
9	3.71
12	3.88
18	4.22
24	4.57
30	5.43
36	5.87

Based on 9" rung spacing

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
556	0.31	313	0.55	200	0.86	139	1.24	102	1.69	78	2.20	62	2.79	50	3.44										

CATALOG NUMBERING EXAMPLE:

09 - 3476 - 0020 - 36

Bottom Type
06 – 6" Rung Spacing
09 – 9" Rung Spacing*
12 – 12" Rung Spacing
** Standard rung spacing*

Tray System Number

Length
0010 – 10'-0"
0012 – 12'-0"
0020* – 20'-0"
0024 – 24'-0"
** Standard for Series 2*

Width
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil

legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3476SF**



RAIL CROSS SECTION



CONNECTOR



AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE:	Solid Flat
NEMA CLASS:	20A, 16B
MATERIAL:	AISI Type 304L Stainless Steel
SIDE RAIL:	4" high with 1 3/4" top flange
LOAD DEPTH:	3"
BOTTOM:	Solid Flat
FINISH:	Plain
CONSTRUCTION:	Arc welded
TRAY SERIES:	Series 2 (5" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 1.0593in^3 S x-x = 0.5860in^4

TRAY WIDTH (IN.)	TRAY WEIGHT (LBS./FT.)
6	4.21
9	4.71
12	5.22
18	6.23
24	7.24
30	8.24
36	9.50

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
556	0.31	313	0.55	200	0.86	139	1.24	102	1.69	78	2.20	62	2.79	50	3.44										

CATALOG NUMBERING EXAMPLE:

SF-3476-0020-36

- **Bottom Type**
  - **SF –** Solid Flat
- **Tray System Number**
- **Length**
  - **0010** – 10'-0"
  - **0012** – 12'-0"
  - **0020*** – 20'-0"
  - **0024** – 24'-0"
  - ** Standard for Series 2*
- **Width**
  - **12** – 12"
  - **18** – 18"
  - **24** – 24"
  - **30** – 30"
  - **36** – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil