CABLOFIL®

# CABLOCUT

## NEW & IMPROVED!

**Cutting head modified to allow more flexibility and easier corner wire cuts**

## Battery powered cable tray cutter

FOR BURR-FREE OPERATIONS

### AT-A-GLANCE

- Open rotating cutting head
- Electronic control and monitoring of cutting operation
- One-button operating concept for controlling all tool functions
- Ergonomic 2-component housing with soft grips for comfortable and safe one-hand operation
- Balanced center of gravity for simple handling and effortless operations
- LED for workplace illumination
- High-performance 18V Lithium-ion batteries with high capacity and extremely short charging time (standard Makita design battery)
- High-performance motors for maximum operating speed
- Energy saving function by switching off the motor when the cutting operation is complete
- Quick motor stop for high user safety
- Automatic retraction when cut is complete
- Manual blade retraction is required
- Multifunction LED for maintenance display and battery charge indication of the battery
- Environmentally-friendly hydraulic oil, quickly biodegradable

### FEATURES & BENEFITS

- **Cablocut** – old electric/manual cutter
- **Hydraulic damping** – extends tool life, reduces oil leakage
- **Easily replaceable shear blades** –user replaceable
- **Shear cut blade design** – no film or grinding
- **Smaller head** – cuts flush with cross wire




legrand®

## Burr-free and clean operations

The battery powered wire mesh cable tray cutter is able to cut Steel or Stainless Steel trays up to 6mm dia easily, quickly, and cleanly.

Special shearing blade geometry – no burr formation – saves time, no follow-up work required

Easily replaceable cutting blade

Hydraulic damping system significantly extends service life – maintenance required only after 20,000 cuts






LED for workplace



Smaller head permits outstanding accessibility and cutting close to the weld point

| CABLOCUT DETAILS | |
|---|---|
| Cutting Range | max. 6mm VA |
| Cutting Force | 24 kN |
| Cutting Time | < 1s |
| Number of Cuts | approx. 300 at 6mm VA |
| Battery Voltage | 18 V (SOLD SEPARATELY) |
| Charging Time | 15 min |
| Weight incl. Battery | 1.9 kg |
| Ambient Temperature | 10 to +40 degrees |

| CAT# | ITEM | DESCRIPTION |
|---|---|---|
| **945064** | CABLOCUT* | Cutter, Case, Spare Blades |
| **945065** | CABLOCUT BLADES | Spare Blades |
| **945066** | CABLOCUT BATTERY* | 18V Li-Ion Battery 1.5 A/HR |
| **945067** | CABLOCUT CHARGER | 120 VAC Quick Charger |

*BATTERY SOLD & SHIPPED SEPARATELY

**RIGID PLASTIC CASE**
room for cutter, battery & charger

**BATTERY***
18 V / 1.5 Ah / Li-Ion

**CHARGER**
Quick-charger for 18 V Li-Ion batteries, 20 V

legrand®

**Electrical Wiring Systems**

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
1.800.723.5175; 905.738.9195
www.legrand.ca

FOLLOW US

©2020 Legrand All Rights Reserved SS3280 04/20