Cablofil

FTEF

TROUGH SPLICE PLATE

FTEF 50 shown



Hardware not included
(341895, 100 per bag)

- M6x12mm square neck carriage bolt (zinc plated)
- M6 serrated flange hex nut (zinc plated)

RELATED PRODUCTS

FTRHR Right-hand Reducer

FTLHR Left-hand Reducer

	PACK	HEIGHT		PG
	PCS	INCHES	MM	
FTEF 50	1	2	50	481562
FTEF 100	1	4	100	X9G71Z

Splices are sold as each

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/12

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil