WIRE BASKET
PLASTIC INSERT WITH SIDES

CF (& ZF) 54, 105, & 150 SERIES
INSERTPPxxx/xxx*

(Replace 'xxx's with appropriate tray depth & width in table)

PART NAME	'A' TRAY DEPTH	'B' TRAY WIDTH
INSERTPP54/100*	2.000	3.810
INSERTPP54/150*	2.000	5.780
INSERTPP54/200*	2.000	7.750
INSERTPP54/300*	2.000	11.690
INSERTPP54/450*	2.000	17.590
#INSERTPP54/500*	2.000	10.840
#INSERTPP54/600*	2.000	12.810
INSERTPP105/100*	3.940	3.810
INSERTPP105/150*	3.940	5.780
INSERTPP105/200*	3.940	7.750
INSERTPP105/300*	3.940	11.690
#INSERTPP105/450*	3.940	9.860
#INSERTPP105/500*	3.940	10.840
#INSERTPP105/600*	3.940	12.810
INSERTPP150/150*	5.900	5.780
INSERTPP150/200*	5.900	7.750
INSERTPP150/300*	5.900	11.690
#INSERTPP150/450*	5.900	9.860
#INSERTPP150/500*	5.900	10.840
#INSERTPP150/600*	5.900	12.810

**** INSERT COLOR SUFFIX, SEE BELOW***

 # THIS SIZE REQUIRES TWO (2) SINGLE PERF PCS BUTTED/OVERLAPPED IN CENTER OF WIRE MESH

PERF LINES ALLOWS EASY FORMING OF SIDES

1 PC STYLE FOR NARROWER WIDTH'S



2 PC STYLE FOR WIDER WIDTH'S (2 ROLLS SUPPLIED)



Material: POLYPROPYLENE
Perf locations: Ref 'A' in table for sides & 'B' for center portion
Thickness: .017"
Length: 200'
Quantity: 1 ROLL (# REPRESENTS 2 ROLLS INCLUDED)
Color: BL (Black), WH (White), YL (Yellow)
Flame Class per UL 94 V-O
Outdoor UV: UL 746C - F1 rating
High Dielectric Strength
Low Moisture Absorption: <0.06%
RoHS Compliant

200' LENGTH ROLLS CAN EASILY BE CUT-TO-LENGTH

"Copyright LNA, Inc. Drawings are proprietary and may not be copied or otherwise duplicated or used without express written permission."

CABCS0715

Legrand
8319 State Rt. 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3250
Fax618-566-4978
www.legrand.us/cablofil