legrand®

Cablofil

FTEC
SQUARE COUPLER

FTEC 50 shown





Hardware included

- M6x12mm square neck carriage bolt (zinc plated)
- M6 serrated flange hex nut (zinc plated)

	PACK	HEIGHT		PG	BL	YL	OR
	PCS	INCHES	MM	STANDARD		OPTIONAL	
FTEC 50	50	2	50	341 561	960 015	960 371	960 194
FTEC 100	50	4	100	341 674	960 018	960 374	960 197

All dimensions are nominal.

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451
OPTIONAL	YL	Carbon Steel ASTM A510 Grade 1008	**Yellow Painted:** Yellow Powder Coated ASTM D 3451
	OR	Carbon Steel ASTM A510 Grade 1008	**Orange Painted:** Orange Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/12

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil