PASS & SEYMOUR®

radiant® Weather-Resistant USB Charging Receptacles, 15A, Tamper-Resistant

Conveniently power mobile devices quickly and reliably outdoors without the need for bulky AC adapters.

WRR26USBAC6

radiant® Weather-Resistant Duplex Receptacles with USB charging capabilities are UL listed to UL498 for weather resistance and comply with section 406.9 of the National Electrical Code. Charge your smart-phones, tablets, and laptops up to 40% faster than 3-5A USB chargers with an Industry-leading charging capacity of 6.0A, shared between both ports. Enjoy the added safety of tamper-resistant receptacles that meet NEC® requirements for tamper-resistance. Protects children: patented shutter system helps prevent improper insertion of foreign objects – now with black "invisi-shutters" for an invisible effect. The external brass back-wire pressure-plate and posted side-wire terminal screws make installation fast and easy.

Features & Benefits

Combination AC USB receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Posted side-wire terminal screws and external back-wire pressure plates for faster termination.

Available with (1) USB Type-A & (1) USB Type-C port or (2) USB Type-C ports to charge the latest mobile devices.



WRR26USBACLA

Type-A and Type-C ports carry minimum rating of 10,000 insertions.

AC USB receptacles are tamper-resistant to meet NEC. Patented shutter system — now with black "invisi-shutters" for an invisible effect preferred by end users — helps prevent improper insertion of foreign objects.

Complies with Section 406.9 of the National Electrical Code for weather resistance.*

- **AC USB receptacles available in 15A, 125V.**
- **Back and side wire termination options** accommodate #14 AWG – #10 AWG stranded and solid copper wire.
- **Multiple color options available.**

*Must be installed with a weatherproof cover. It is recommended that these devices are installed in a wall box measuring at least 3" x 2" x 2-1/2" to ensure proper NEC Article 314 box fill requirements. For retrofit applications a Weatherproof extension ring may be required on boxes with less depth than 2-1/2".

3rd Party Compliance

cULus listed, UL listed. Complies with test requirements UL 498, UL 1310
CSA C22.2 No. 42, CSA c22.2 No. 223

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Maximum Temperature Rise	30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current
No-Load Power Draw	10.7 mW Meets Department of Energy (DoE) Level VI requirement
FCC Part 15	Class B
Mechanical	
Terminal Accommodation	Back and side wire termination options accommodate #14 AWG - #10 AWG stranded and solid copper wire.
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
RoHS	Compliant

Materials	
Face	UV protected Polycarbonate
Back Body	Nylon
Line Contacts	CDA 260 Brass
Mounting Strap	G90 Galvanized plated steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate for Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel



WRR26USBACLA

Warranty

1 Year

Ordering Information

Ultra-Fast Weather-Resistant USB Type AC Chargers with Duplex Tamper-Resistant Receptacles

	Rating				3rd Party Compliance		
Catalog Number	A	V	Color	Total Charging Capacity	UL498 UL1310		C22.2 No. 42 C22.2 No. 223
WRR26USBAC6BK	15	125	Black	6 Amp	•	•	•
WRR26USBAC6I	15	125	Ivory	6 Amp	•	•	•
WRR26USBAC6LA	15	125	Light Almond	6 Amp	•	•	•
WRR26USBAC6W	15	125	White	6 Amp	•	•	•

NEMA 5-15R

Vertical Markets

- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection...

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Combination Devices**
- **Adjustable Night Lights**
- **Screwless Wall Plates**
- **Sensors**
- **Home Automation Controls**
- **Wireless Qi & USB charging receptacles**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

905.738.9195
www.legrand.ca

FOLLOW US

CS3038 November 2019 **©2019 Legrand All Rights Reserved**