DLM SEGMENT NETWORK TO IP ROUTER

NB-ROUTER

Routes one BACnet MS/TP Segment Network to BACnet IP

Simple configuration using a standard web browser

Compatible with DLM Network Controller or third party BACnet building automation systems

BACnet/IP or BACnet Ethernet connectivity

DESCRIPTION

The NB-ROUTER provides a connection point between a single Digital Lighting Management (DLM) segment network and an Ethernet LAN. The router has a rugged metal enclosure with an integral DIN rail mounting clip.

OPERATION

The NB-ROUTER provides a browser-based interface for set up and configuration. Using an assigned IP address and additional Ethernet and BACnet MS/TP settings, the device automatically routes network communication between the segment network and an IP network.

APPLICATIONS

The NB-ROUTER is perfect for applications with DLM segment networks originating from multiple locations, or for routing a segment network to a BAS via BACnet IP or BACnet Ethernet.

SPECIFICATIONS

- Operating voltage: 24 VAC/VDC from 120 VAC cord-end power supply (included)
- Quick disconnect 4-pin power connector
- Power LED
- RJ45 Ethernet port
- Ethernet and MS/TP activity LEDs
- Quick disconnect 3-wire MS/TP connector
- DIN-rail mounting clip
- Five year warranty

NETWORK WIRING



DIMENSIONS



ORDERING INFORMATION

Catalog #		Description	Weight
☐	NB-ROUTER	DLM Segment Network to BACnet IP Router	1 pound

BACnet® is a registered trademark of ASHRAE.

27566r4 Rev 09/26

PROJECT		LOCATION/ TYPE	