legrand®

Pass & Seymour

Extra Heavy-Duty Receptacles
PlugTail™ Devices
Tamper-Resistant 15 & 20A, 125V

PTTR62, PTTR63

PlugTail™. The fastest, most consistent and reliable wiring devices – ever.

Factory-terminated wiring devices are what you get with PlugTail wiring devices. Wiring devices are terminated the same no matter what the skill level. The UL-Listed connectors are keyed to ensure proper wiring installation into each extra heavy-duty receptacle. Just snap the connector into the back of the device. And a sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle.



FEATURES & BENEFITS

Auto-ground clip assures positive ground.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Dual mechanical shutter system to help prevent insertion of foreign objects.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.



PTTR63-W

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.



Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

No exposed terminals before, during, or after installation increases safety at all phases of product life.

FIELD USES/VERTICAL MARKETS

- Industrial
- Health Care
- Education
- Institutional

legrand®
Pass & Seymour

Extra Heavy-Duty Receptacles
PlugTail™ Devices
Tamper-Resistant 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A.	Rating V.	Color	NEMA Config. No.
Duplex Receptacles				
PTTR62-I	15	125	Ivory	5-15R
PTTR62-W	15	125	White	5-15R
PTTR62	15	125	Brown	5-15R
PTTR62-GRY	15	125	Gray	5-15R
PTTR62-BK	15	125	Black	5-15R
PTTR62-BL	15	125	Blue	5-15R
PTTR62-RED	15	125	Red	5-15R
PTTR62-LA	15	125	Light Almond	5-15R
PTTR63-I	20	125	Ivory	5-20R
PTTR63-W	20	125	White	5-20R
PTTR63	20	125	Brown	5-20R
PTTR63-GRY	20	125	Gray	5-20R
PTTR63-BK	20	125	Black	5-20R
PTTR63-BL	20	125	Blue	5-20R
PTTR63-RED	20	125	Red	5-20R
PTTR63-LA	20	125	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
PlugTail Connectors — Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

NEMA 5-15R

NEMA 5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Extra Heavy-Duty Receptacles
PlugTail™ Devices
Tamper-Resistant 15 & 20A, 125V

legrand®
Pass & Seymour

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498.
Federal Specification WC596.

Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

Plug Tail Receptacle Materials

Face	Nylon	Integral Ground System	.036 260 Brass
Back Body	Nylon	Assembly Drive Screw	Zinc-Plated Steel
Line Contacts	.036 688 Brass	Auto-Ground Clip	Brass
Mounting Strap	.050 260 Brass	Mounting Screws	Tri-Drive Steel

Plug Tail Connector Materials

Housing	Polycarbonate	Contacts	.036 688 Brass

Warranty

1 Year



Dimensions for 15 & 20 Amp



PTRA6STR

COMPLEMENTARY DEVICES & ACCESSORIES



PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant Hospital Grade



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Specification Grade

WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Bulk Solutions

legrand®
Pass & Seymour

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone:905.738.9195

SF1503R1 – Updated May 2010 – For latest specs visit www.legrand.us/passandseymour

© Copyright 2010 All Rights Reserved Legrand/Pass & Seymour EWS/GGXTP