NOTES:

ELECTRICAL

Electrical Insulation Resistance : 500MΩ min. @ 100V d.c

Dielectric Withstanding Voltage : 1000V d.c. or a.c. Peak Contact to Contact @ 60Hz for 1 minute

MECHANICAL

Insertion / Extraction Life : 750 Cycles Minimum

IDC Wire Gauge : 22 ~ 24 AWG

Housing : High-Impact, Flame-Retardant Plastic, UL 94V-0

Spring Wire : Phosphor Bronze Alloy Plated With 50 micro-inch of Gold

IDC : Phosphor Bronze Alloy With 100 micro-inch 100% Sn Alloy









PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF On-Q/LEGRAND. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF On-Q/LEGRAND IS PROHIBITED. DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE.

legrand®
P.O. Box 60907
Middletown, PA 17106-0907
1-800-321-2343

TITLE: 1X6 BRIDGED TELEPHONE BOARD

SIZE	DWG NO	FILE NAME	CUST REV
A	TM0106	CD-TM0106	1

REVISED DATE	SCALE	SHEET
15/09/22	NONE	1 OF 1

ACAD